


## Set axial EAMM-A-K48-60G

Numar piesa: 557986

FESTO



### Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Cuplu transmisibil	12.5 Nm
Greutate produs	300 g
Cod de interfata actuator	K48
Codul interfetei motor In	60G
Nota privind materialele	Conform RoHS