

Cuplaj EAMC-30-32-5-6

Numar piesa: 561333

FESTO



Fisa de date

| Caracteristica | Valoare |
|------------------------------|----------------|
| Diametrul de montare 1 | 5 mm |
| Diametru de montare 2 | 6 mm |
| Dimensiune | 30 |
| Lungime nominala | 32 mm |
| Pozitie de instalare | orice |
| Turatie max. | 8000 1/min |
| Conformitatea LABS | VDMA24364-B2-L |
| Temperatura de depozitare | -25 °C...60 °C |
| Umiditate relativa | 0 - 95 % |
| Temperatura ambianta | -25 °C...60 °C |
| Momentul de inertie al masei | 5.87 000065 |
| Cuplu transmisibil | 3.5 Nm |
| Greutate produs | 48 g |
| Nota privind materialele | Conform RoHS |