

## Set axial EAMM-A-P6-38A-55A

Numar piesa: 562647

FESTO



### Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Cuplu transmisibil	6.5 Nm
Greutate produs	130 g
Cod de interfata actuator	P6-38A
Codul interfetei motor In	55A
Cod de interfata carcasa de cuplare	38A
Nota privind materialele	Conform RoHS