


Protecție aerisire VABD-D3-SN-G14

Numar piesa: 563400

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Presiune de lucru	0 MPa...1 MPa 0 bar...10 bar
Protectie la explozie	Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Conformitatea LABS	VDMA24364 zona III
Tip de protectie	IP65
Temperatura ambianta	-50 °C...60 °C
Tipul de montare	insurubabil cu filet exterior
Nota privind materialele	Conform RoHS
Material garnituri	EPDM
Material surub de aerisire	PA