

kit burduf EADB-V1-32-S10-100

Cod: 570262

FESTO



Fisa tehnica

Caracteristica	valoare
diametru exterior	46 mm
marime de fabricatie	32
Gama cursa	10 ... 100 mm
Extensie tija piston	44 mm
design	rotund
pozitie instalare	oricare
structura constructiva	kit burduf cu exhaustare pe canal
clasa de rezistenta la coroziune KBK	3
Rezistenta chimica	praf span ulei grasime Benzina
tip de protectie	IP65 conform IEC 60529
temperatura mediului	-10 ... 80 °C
masa miscata	35 g
greutate produs	77 g
tip fixare	prin impingere cu stift filetat
racord pneumatic	G1/8
indicatie material	conform RoHS
Informatii material: Componente adaptor	aliaj maleabil aluminiu eloxat
informatii referitoare la material pentru etansari	NBR
Informatii material: Burduf	NBR
Informatii material stifturi filetate	otel inoxidabil inalt aliat