

Kit fixare SAMH-S-N8-S-MK

Numar piesa: 575815

FESTO



Fisa de date

Caracteristica	Valoare
Design	pentru canelura T
Nota privind materialele	Conform RoHS
Temperatura ambianta	-40 °C...85 °C
Tipul de montare	cu blocare insurubat fix poate fi introdus in canelura de sus
Cuplu de strangere max.	0.6 Nm
Greutate produs	1.88 g
Material dop de obturare	PA
Material bloc terminal	otel aliaj inalt
Clasa de rezistenta la coroziune KBK	3 - stres intens de coroziune
Conformitatea LABS	VDMA24364-B2-L