

Placa de capat VMPAC-EPL-MP-SD44

Numar piesa: 576559

FESTO



Fisa de date

Caracteristica	Valoare
Presiune de lucru	-0.9 bar...8 bar
Presiunea de control	3 bar...8 bar
Clasa de rezistenta la coroziune KBK	4 - Mediu coroziv deosebit de puternic
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-5 °C...50 °C
Greutate produs	246 g
Conector pneumatic 3	G3/8
Conexiune pneumatica 5	G3/8
Nota privind materialele	Conform RoHS
Material carcasa	Ranforsat cu PA