

## Racord L NPFC-L-2G14-F

Numar piesa: 8030210

FESTO



### Fisa de date

| Caracteristica                       | Valoare  |
|--------------------------------------|--|
| Material racord filetat              | Alama, nichelata                               |
| Unitate de ambalare                  | 10   |
| Presiune de lucru                    | -0.95 bar...50 bar                             |
| Mediu de operare                     | Aer comprimat conform ISO 8573-1:2010 [-::-:-] |
| Clasa de rezistenta la coroziune KBK | 1 - stres redus la coroziune                   |
| Conformitatea LABS                   | VDMA24364-B1/B2-L                              |
| Temperatura ambianta                 | -20 °C...150 °C                                |
| Greutate produs                      | 36.2 g   |
| Conector pneumatic 1                 | G1/4   |
| Conexiune pneumatica 2               | G1/4   |
| Nota privind materialele             | Conform RoHS                                   |