


Placa racordare VMPA2-FB-AP-2-1-S0-RV

Numar piesa: 8034552

FESTO



Fisa de date

Caracteristica	Valoare
Latime	53 mm
Lungime	107.3 mm
Dimensiune grila	21 mm
Numarul max. de pozitii de ventil	2
Presiune de lucru	-0.09 MPa...1 MPa -0.9 bar...10 bar
Presiunea de control	0.3 MPa...0.8 MPa 3 bar...8 bar
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:4:4]
Clasa de rezistenta la coroziune KBK	0 - nu este afectat de coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-5 °C...50 °C
Greutate produs	190 g
Nota privind materialele	Conform RoHS
Materialul placii de racordare	Aluminiu turnat sub presiune