

Tub plastic PTFEN-3/8-NT-150

Numar piesa: 8061182

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior	9.53 mm
raza de indoire relevanta pentru debit	100 mm
Ø interior	6.5 mm
Raza min. de indoire	63 mm
Nota de aplicare	Furtun fara imprimare
Presiune de functionare interval complet de temperatura	-0.095 MPa...0.5 MPa -0.95 bar...5 bar -13.775 000032...72.5 000032
Presiune de lucru in functie de temperatura	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 000032...174 000032
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Material de testare la foc	UL94 V-0
Conformitatea LABS	VDMA24364-B1/B2-L
Clasa de puritate a incaperii	Element instalat static, fara posibilitate de evaluare semnificativa conform ISO 14644-1
Siguranta alimentara	vedeti informatii detaliate despre material
Temperatura ambianta	-20 °C...150 °C
Greutatea produsului in functie de lungime	0.084 000015
Conexiune pneumatica	pentru conector cu Ø exterior 3/8"
Culoare	natura
Duritate Shore	D 55 +/-5
Nota privind materialele	Conform RoHS
Material furtun	PTFE