


Ventuza vacuum OGVM-40X90-GV-N-G14F

Numar piesa: 8073864

FESTO



Fisa de date

Caracteristica	Valoare
Ventuza de compensare a inaltimii	6 mm
Raza min. a piesei de prelucrat	35 mm
Latimea nominala	6 mm
Dimensiunea ventuzei	40x90 mm
Volum de aspiratie	15.8 cm ³
Pozitie de conectare	sus
Pozitie de instalare	orice
Forma de ventuza	forma ovala de clopot
Presiune de lucru	-95 kPa...0 kPa -0.95 bar...0 bar -13.775 000032...0 000032
Presiunea nominala de functionare	-60 kPa -0.6 bar
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:-:-]
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	-20 °C...80 °C
Fora de mentinere la presiune de lucru nominala	311 N
Fora transversala verticala la presiunea de lucru nominala	192 N
Greutate produs	40 g
Tipul de montare	prin racordul de vid
Racord de vacuum	Filet interior G1/4
Culoare	negru
Duritate Shore	60 +/- 5
Material pivot de insurubare	Aliaj de aluminiu forjat
Nota privind materialele	Conform RoHS
Material ventuze	NBR