

## Echer fixare PAMP-MB-64

Numar piesa: 8081356

FESTO



### Fisa de date

Caracteristica	Valoare
Dimensiune	64
Seria	P
Clasa de rezistenta la coroziune KBK	4 - Mediu coroziv deosebit de puternic
Conformitatea LABS	VDMA24364-B2-L
Cuplu de strangere max. la fixarea ventilului	5 Nm
Temperatura medie	-60 °C...80 °C
Temperatura ambianta	-60 °C...80 °C
Greutate produs	119 g
Nota privind materialele	Conform RoHS
Material suruburi	otel inoxidabil inalt aliat
Material echer	otel inoxidabil inalt aliat