

Compensator de moment DARD-L8-20-S

Numar piesa: 8081466

FESTO



Fisa de date

| Caracteristica | Valoare |
|--|------------------------------|
| Dimensiune | 20 |
| Abatere radiala +/- | 2.5 mm |
| Clasa de rezistenta la coroziune KBK | 1 - stres redus la coroziune |
| Conformitatea LABS | VDMA24364-B1/B2-L |
| Temperatura ambianta | 0 °C...60 °C |
| Sarcina maxima admisibila pe termen scurt in directia fortei +/- | 1100 N |
| Sarcina maxim admisibila pe termen lung in directia fortei +/- | 550 N |
| Greutate produs | 137 g |
| Nota privind materialele | Conform RoHS fara cupru |
| Material adaptor | Aluminiu, anodizat |
| Material suruburi | Otel, galvanizat |