

Set paralel EAMM-U-65-T42-60AA-87

Numar piesa: 8093189

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	65
Centru	87 mm
Pozitie de instalare	orice
Raportul de transmisie	1:1
Turatie max.	3000 1/min
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-20 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	0 °C...50 °C
Momentul de inertie al masei	41.2 000065
Cuplu de antrenare in gol	0.22 Nm
Cuplu transmisibil	3 Nm
Greutate produs	583 g
Cod de interfata actuator	T42
Codul interfetei motor In	60AA
Nota privind materialele	Conform RoHS