


Set paralel EAMM-U-38-V25-35A-63

Numar piesa: 8093286

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	38
Centru	63 mm
Pozitie de instalare	orice
Raportul de transmisie	1:1
Turatie max.	3600 1/min
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-20 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	0 °C...50 °C
Momentul de inertie al masei	4.35 000065
Cuplu de antrenare in gol	0.05 Nm
Cuplu transmisibil	0.5 Nm
Greutate produs	218 g
Cod de interfata actuator	V25
Codul interfetei motor In	35A 23AB
Nota privind materialele	Conform RoHS