

# Bobina VACC-S18-120-K4-1UF-NE4ME

Cod: 8118262

FESTO



## Fisa tehnica

Caracteristica	valoare
tip de actionare	electric
pozitie instalare	Oricare
Afisarea pozitiei de comutare	nu
Protectie interna	Siguranta de protectie
Durata de anclansare	100 %
Clasa izolatie	H
Caracteristica bobina	24 V AC: 50/60 Hz, putere 12 VA 24 V DC: 12 W
Oscilatii admisibile ale tensiunii	-15 % / +10 %
Certificat ATEX in afara UE	EPL Db (CN) EPL Gb (CN)
Departament eliberare certificate	GYJ17.1237X
Tip gaz cu protectie la explozie si aprindere	Ex e mb IIC T4 Gb
Tip praf cu protectie la aprindere si explozie	Ex tD A21 IP66 T120°C
Protectie la explozie temperatura ambientala	T4, T120°C: -25°C ≤ Ta ≤ +40°C
Conformitatea PWIS	VDMA24364-zona III
Tip de protectie	IP66
Greutate produs	580 g
Conectare electrica	Cutie terminal, cablu filetat M20x1.5
Indicatie material	conform RoHS