

Portal tridimensional YXCR-1-B

Numar piesa: 8122268

FESTO



Fisa de date

Caracteristica	Valoare
Planeitatea necesara a suprafetelor de cultivare	0.1 MMM
Pozitie de instalare	orizontala
Structura constructiva	Sistem de portal spatial cu module de actionare electrica si pneumatica
Ciclu de lucru	100%
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-20 °C...60 °C
Umiditate relativa	0 - 90 %
Tip de protectie	IP40
Temperatura ambianta	5 °C...45 °C
Interval de intretinere	2500 km
Nota privind materialele	Conform RoHS
Material placa de adaptare	Aluminiu, anodizat
Material echer de fixare	Otel inoxidabil aliaj inalt
Material lanturi energetice	Ranforsat cu PA