


Reductor EMGA-40-P-G12-SST-42

Cod: 8141763

FESTO



Fisa tehnica

Caracteristica	valoare
Transmisie flansa	40 mm
Motor cu flansa	42 mm
Joc de rasucire	0,31 deg
tipul reductorului	Angrenaj planetar
Raport de transmisie	12:1
Viteza maxima de intrare	18.000 1/min
Temperatura de operare reductor	-25 ... 90 °C
Conformitatea PWIS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de actionare continua	20 Nm
Momentul de inertie al angrenajului	0,026 kgcm ²
Cuplu maxim iesire	32 Nm
Eficienta maxima	96 %
rigiditate la torsiune	1 Nm/arcmin
Greutate produs	450 g
Interfata reductor arbore de iesire	40G
Interfata reductor arbore de antrenare	42A
Indicatie material	conform RoHS