

Adaptor AD-G1/2-1/2NPT-I

Numar piesa: 9398

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	14.3 mm
Presiune de functionare interval complet de temperatura	-0.95 bar...10 bar
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-10 °C...60 °C
Cuplu de strangere max. conexiune pneumatica 1	40 Nm
Cuplu de strangere max. conexiune pneumatica 2	28 Nm
Cuplu de strangere nominal	47.9 Nm
Toleranta fata de cuplul de strangere nominal	± 20 %
Greutate produs	51.89 g
Conector pneumatic 1	Filet exterior G1/2
Conexiune pneumatica 2	Filet interior 1/2 NPT
Nota privind materialele	Conform RoHS
Material garnituri	PVC
Material carcasa	Otel galvanizat