

# Priključna letva VABM-C8-12E-G14-32-PT-L

Broj artikla: 1247986

Classic - nicht für Neukonstruktionen verwenden

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Mera mreže	12 mm
Maks. broj ventilskih mesta	32
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Klasa korozione otpornosti KBK	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Maks. pritezni moment, pričvršćenje ventila	0,6 Nm
Maks. pritezni moment, zidna montaža	5 Nm
Težina proizvoda	1.982 g
Pneumatski priključak 1	G1/4
Pneumatski priključak 3	G1/4
Pneumatski priključak 5	G1/4