

Vod resolvera



NEBM-M23G12-E-10-N-S1G9

Broj artikla: 1732654

Komponenta koja će prestati da se proizvodi

[odgovara za servomotor EMMS-AS-...](#)

FESTO



Tehnički podaci

Svojstvo	Vrednost
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M23x1
Electrical connection 1, number of pins/wires	12
Electrical connection 1, occupied pins/wires	6
Electrical connection 2, function	Controller side
Electrical connection 2, design	ugaono
Electrical connection 2, connection type	Utikači
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	Sub-D
Electrical connection 2, number of pins/wires	9
Electrical connection 2, occupied pins/wires	7
Područje pogonskog napona DC	0 ... 30 V
Nazivni pogonski napon DC	24 V
Područje pogonskog napona AC	0 ... 30 V
Nazivni pogonski napon AC	24 V
Dužina kabela	10 m
Svojstvo kabela	prikladno za energetski lanac
Bending radius, flexible cable installation	≥ 98 mm
Prečnik kabela	8,3 mm
Struktura kabela	3x(2x0,14)+2x(0,5) zaslonjeno
Nazivni presek provodnika	0,14 mm ² 0,5 mm ²
Mehanička zaštita	IP65
Note on degree of protection	IP30 for plug connector Sub-D u montiranom stanju
Temperatura okoline	-50 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-40 ... 75 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Stepen zagađenja	3
Klasa korozijske otpornosti KBK	0 - No corrosion stress
Material cable sheath	TPE-U(PUR)