


Motorski vod NEBM-M40G8-E- -Q10N-LE8

Broj artikla: 1750244

Komponenta koja će prestati da se proizvodi

For EMMS-AS-190 with CMMP-AS.

FESTO



Prikaz primera

Tehnički podaci

Svojstvo	Vrednost
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M40x1,5
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
Područje pogonskog napona DC	0 ... 630 V
Note on operating voltage range DC	0 - 300 V for 0.75 mm ²
Područje pogonskog napona AC	0 ... 630 V
Note on operating voltage range AC	0 - 300 V for 0.75 mm ²
Strujna opteretivost kod 40°C	22 A
Note on acceptable current load at 40°C	12 A for 0.75 mm ²
Čvrstoća na udarno naprezanje	4 kV
Note on surge resistance	2.5 kV for 0.75 mm ²
Dužina kabla	1 ... 25 m
Svojstvo kabla	prikladno za energetski lanac
Bending radius, fixed cable installation	≥ 70 mm
Bending radius, flexible cable installation	≥ 140 mm
Prečnik kabla	14 mm
Struktura kabla	4x2,5+2x(2x0,75) zaslonjeno
Nazivni presek provodnika	0,75 mm ² 2,5 mm ²
Krajevi žica	Završetak žice
Mehanička zaštita	IP65
Note on degree of protection	u montiranom stanju
Temperatura okoline	-50 ... 90 °C
Temperatura okoline kod pokretnog postepenja kablova	-40 ... 90 °C
CE znak (vidi izjavu o usklađenosti)	prema EU-niski napon-smernica in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	0 - No corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	narančasto
Material insulation	TPE-E