

Slobodni hod

FLSR-12-R

Broj artikla: 30929

Classic - nicht für Neukonstruktionen verwenden

za zakretni pogon DSR.

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



Tehnički podaci

Svojstvo	Vrednost
Veličina	12
Smer obrtanja	Desni hod
Položaj ugradnje	proizvoljno
PWIS conformity	VDMA24364-B2-L
Temperatura okoline	-10 ... 60 °C
Theoretical torque at 0.6 MPa (6 bar, 87 psi)	1 Nm
Težina proizvoda	220 g
Material housing	Aluminijumski liv
Material sleeve	Čelik za kaljenje
Material shaft	Čelik za kaljenje