

# Slobodni hod

## FLSR-10-R

Broj artikla: 33299

Classic - nicht für Neukonstruktionen verwenden

za zakretni pogon DSR.

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Veličina	10
Smer obrtanja	Desni hod
Položaj ugradnje	proizvoljno
PWIS conformity	VDMA24364-B2-L
Temperatura okoline	-10 ... 60 °C
Theoretical torque at 0.6 MPa (6 bar, 87 psi)	0,53 Nm
Težina proizvoda	100 g
Material housing	Aluminijumski liv
Material sleeve	Čelik za kaljenje
Material shaft	Čelik za kaljenje