

Prigušivač zvuka U-PK-3

Broj artikla: 4646

FESTO

For reducing noise and avoiding contamination at the exhaust ports of pneumatic components.



Tehnički podaci

Svojstvo	Vrednost
Položaj ugradnje	proizvoljno
Operating pressure MPa	0 ... 1 MPa
Pogonski pritisak	0 ... 10 bar
Protok prema atmosferi	310 l/min
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-]
Napomena o mediju pogona i upravljanja	Moguć nautljeni pogon
PWIS conformity	VDMA24364-B1/B2-L
Nivo zvučnog pritiska	70 dB(A)
Temperatura okoline	-10 ... 70 °C
Težina proizvoda	4,5 g
Pneumatski priključak	PK-3
Material of silencer insert	Bronza
Material of threaded plug	Mesing
Materijal - napomena	RoHS komformnost