

Vod utičnice SIM-M12-8GD-5-PU

Broj artikla: 525618

FESTO



Tehnički podaci

| Svojstvo | Vrednost |
|--|--|
| Odgovara standardu | DIN 47100 EN 61076-2-101 |
| Cable identification | Without inscription label holder |
| Težina proizvoda | 343 g |
| Electrical connection 1, function | Field device side |
| Electrical connection 1, design | okruglo |
| Electrical connection 1, connection type | Utičnica |
| Electrical connection 1, cable outlet | Ravno |
| Electrical connection 1, connection technology | M12x1, A-coded in accordance with EN 61076-2-101 |
| Electrical connection 1, number of pins/wires | 8 |
| Electrical connection 1, occupied pins/wires | 8 |
| Electrical connection 1, type of mounting | Screw lock |
| Electrical connection 2, function | Controller side |
| Electrical connection 2, connection type | Kabl |
| Electrical connection 2, connection technology | otvoreni kraj |
| Electrical connection 2, number of pins/wires | 8 |
| Electrical connection 2, occupied pins/wires | 8 |
| Područje pogonskog napona DC | 0 ... 30 V |
| Područje pogonskog napona AC | 0 ... 30 V |
| Strujna opteretivost kod 40°C | 2 A |
| Čvrstoća na udarno naprezanje | 0,8 kV |
| Dužina kabla | 5 m |
| Svojstvo kabla | Standard |
| Bending radius, fixed cable installation | ≥ 32 mm |
| Bending radius, flexible cable installation | ≥ 66 mm |
| Prečnik kabla | 6,3 mm |
| Odstupanje prečnika kabla | ± 0,2 mm |
| Struktura kabla | 8x0,25 zaslonjeno |
| Nazivni presek provodnika | 0,25 mm ² |
| Krajevi žica | pocinkovano |
| Mehanička zaštita | IP67 |
| Note on degree of protection | u montiranom stanju |
| Temperatura okoline | -25 ... 80 °C |
| Temperatura okoline kod pokretnog postepenja kablova | -5 ... 80 °C |
| CE znak (vidi izjavu o usklađenosti) | in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| PWIS conformity | VDMA24364-B2-L |
| Materijal - napomena | RoHS komformnost |
| Stepen zagađenja | 3 |
| Klasa korozione otpornosti KBK | 2 - Moderate corrosion stress |
| Material cable sheath | TPE-U(PUR) |
| Boja izolacije | sivo |
| Material housing | TPE-U(PUR) |
| Material screw-type lock | Nickel-plated brass |
| Material seals | FPM |
| Material electrical contact | Gold-plated bronze |
| Material insulation | PP |