


# Vod upravljanja KES-MC-1-SUB-9-10

Broj artikla: 537925

Komponenta koja će prestati da se proizvodi

[odgovara za MTR-DCI-...](#)

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	9
Electrical connection 1, occupied pins/wires	9
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	10
Electrical connection 2, occupied pins/wires	9
Područje pogonskog napona DC	0 ... 24 V
Dužina kabla	10 m
Svojstvo kabla	prikladno za energetski lanac
Bending radius, fixed cable installation	≥ 28 mm
Bending radius, flexible cable installation	≥ 51 mm
Prečnik kabla	6,8 mm
Struktura kabla	10x0,14 zaslonjeno
Nazivni presek provodnika	0,14 mm <sup>2</sup>
Krajevi žica	Pin terminal
Mehanička zaštita	IP54
Note on degree of protection	u montiranom stanju
Temperatura okoline	0 ... 50 °C
Materijal - napomena	Sadrži PWIS
Klasa korozione otpornosti KBK	0 - No corrosion stress