

Kabl za napajanje KPWR-MC-1-SUB-9HC-10

Broj artikla: 537933

Komponenta koja će prestati da se proizvodi

[odgovara za MTR-DCI...](#)

FESTO



Tehnički podaci

Svojstvo	Vrednost
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	Sub-D Mixed
Electrical connection 1, number of pins/wires	2
Electrical connection 1, occupied pins/wires	2
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	2
Electrical connection 2, occupied pins/wires	2
Područje pogonskog napona DC	24 ... 48 V
Dužina kabela	10 m
Svojstvo kabela	prikladno za energetski lanac
Bending radius, flexible cable installation	≥ 64 mm
Prečnik kabela	8,6 mm
Struktura kabela	2x1,5 zaslonjeno
Nazivni presek provodnika	1,5 mm ²
Krajevi žica	Pin terminal
Mehanička zaštita	IP54
Note on degree of protection	u montiranom stanju
Temperatura okoline	0 ... 50 °C