

Kabl za napajanje KPWR-MC-1-SUB-15HC-10



Broj artikla: 538916

Komponenta koja će prestati da se proizvodi

za priključak napajanja opterećenja i logike.

Tip se više ne proizvodi. Isporučuje se do 2020. Vidi Support Portal za alternativni proizvod.

FESTO



Tehnički podaci

Svojstvo	Vrednost
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	Sub-D Mixed
Electrical connection 1, number of pins/wires	7
Electrical connection 1, occupied pins/wires	6
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	6
Electrical connection 2, occupied pins/wires	6
Područje pogonskog napona DC	0 ... 24 V
Dužina kabla	10 m
Svojstvo kabla	prikladno za energetski lanac
Bending radius, fixed cable installation	≥ 50 mm
Bending radius, flexible cable installation	≥ 100 mm
Prečnik kabla	10 mm
Struktura kabla	2x2,5+2x(2x0,34) zaslonjeno
Nazivni presek provodnika	0,34 mm ² 2,5 mm ²
Krajevi žica	Pin terminal
Mehanička zaštita	IP54
Note on degree of protection	u montiranom stanju
Temperatura okoline	0 ... 40 °C
Temperatura okoline kod pokretnog postepenja kablova	-25 ... 60 °C
Materijal - napomena	Sadrži PWIS
Klasa korozione otpornosti KBK	0 - No corrosion stress
Material cable sheath	TPE-U(PUR)
Material insulation	TPE-E