

Vod upravljanja KES-MC-1-SUB-15-5



Broj artikla: 538920

Komponenta koja će prestati da se proizvodi

za spajanje UI/Izl za priključak na proizvoljno upravljanje.

Tip se više ne proizvodi. Isporučuje se do 2020. Vidi Support Portal za alternativni proizvod.

FESTO



Tehnički podaci

Svojstvo	Vrednost
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	15
Electrical connection 1, occupied pins/wires	15
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	18
Electrical connection 2, occupied pins/wires	15
Područje pogonskog napona DC	0 ... 24 V
Dužina kabla	5 m
Svojstvo kabla	prikladno za energetski lanac
Bending radius, fixed cable installation	≥ 40 mm
Bending radius, flexible cable installation	≥ 75 mm
Prečnik kabla	10 mm
Struktura kabla	18x0,34 zaslonjeno
Nazivni presek provodnika	0,34 mm ²
Krajevi žica	Završetak žice
Mehanička zaštita	IP54
Note on degree of protection	u montiranom stanju
Temperatura okoline	0 ... 40 °C
Materijal - napomena	Sadrži PWIS
Klasa korozione otpornosti KBK	0 - No corrosion stress