


Vod utičnice

NEBU-M12W8-K-2-N-LE8

Broj artikla: 542256

FESTO



Tehnički podaci

Svojstvo	Vrednost
Odgovara standardu	EN 61076-2-101
Cable identification	Without inscription label holder
Težina proizvoda	125 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
Područje pogonskog napona DC	0 ... 30 V
Područje pogonskog napona AC	0 ... 30 V
Strujna opteretivost kod 40°C	2 A
Čvrstoća na udarno naprezanje	0,8 kV
Dužina kabla	2 m
Svojstvo kabla	Standard
Bending radius, fixed cable installation	≥ 32 mm
Bending radius, flexible cable installation	≥ 66 mm
Prečnik kabla	6,3 mm
Odstupanje prečnika kabla	± 0,2 mm
Struktura kabla	8x0,25 zaslonjeno
Nazivni presek provodnika	0,25 mm ²
Krajevi žica	pocinkovano
Mehanička zaštita	IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-25 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo
Material housing	TPE-U(PUR)
Material of union nut	Mesing niklovan
Material seals	NBR
Material electrical contact	Brass, gold-plated
Material insulation	PP