


Motorski vod NEBM-T1G8-E- -Q7N-LE8

Broj artikla: 550309

FESTO

For EMMS-AS-40/55 with encoder with CMMP-AS.



Tehnički podaci

Svojstvo	Vrednost
Odgovara standardu	EN 61984
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	ITT M3
Electrical connection 1, number of pins/wires	10
Electrical connection 1, occupied pins/wires	8
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
Područje pogonskog napona DC	0 ... 630 V
Note on operating voltage range DC	0 - 48 V for 0.25 mm ²
Područje pogonskog napona AC	0 ... 630 V
Note on operating voltage range AC	0 - 48 V for 0.25 mm ²
Strujna opteretivost kod 40°C	12 A
Note on acceptable current load at 40°C	3 A for 0.25 mm ²
Čvrstoća na udarno naprezanje	4 kV
Note on surge resistance	0.5 kV for 0.25 mm ²
Dužina kabela	1 ... 25 m
Svojstvo kabela	prikladno za energetski lanac
Bending radius, fixed cable installation	≥ 55 mm
Bending radius, flexible cable installation	≥ 110 mm
Prečnik kabela	11 mm
Struktura kabela	4x0,75+2x(2x0,25) zaslonjeno
Nazivni presek provodnika	0,25 mm ² 0,75 mm ²
Krajevi žica	Završetak žice
Mehanička zaštita	IP65
Note on degree of protection	u montiranom stanju
Temperatura okoline	-50 ... 90 °C
Temperatura okoline kod pokretnog postepenja kablova	-40 ... 90 °C
CE znak (vidi izjavu u usklađenosti)	prema EU-niski napon-smernica in accordance with EU RoHS directive
Materijal - napomena	RoHS komfornost
Stepen zagađenja	3
Material cable sheath	TPE-U(PUR)
Boja izolacije	narandžasto