

Vod enkodera



NEBM-M12W8-E-10-N-S1G15

Broj artikla: 550319

Komponenta koja će prestati da se proizvodi

[odgovara za servomotor EMMS-AS-...](#)

FESTO



Tehnički podaci

Svojstvo	Vrednost
Odgovara standardu	EN 61984
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 2, function	Controller side
Electrical connection 2, design	ugaono
Electrical connection 2, connection type	Utikači
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	Sub-D
Electrical connection 2, number of pins/wires	15
Electrical connection 2, occupied pins/wires	8
Područje pogonskog napona DC	0 ... 30 V
Nazivni pogonski napon DC	24 V
Područje pogonskog napona AC	0 ... 30 V
Nazivni pogonski napon AC	24 V
Strujna opteretivost kod 40°C	3 A
Note on acceptable current load at 40°C	2 A for 0.14 mm ²
Čvrstoća na udarno naprezanje	0,5 kV
Dužina kabela	10 m
Svojstvo kabela	prikladno za energetski lanac
Bending radius, fixed cable installation	≥ 20 mm
Bending radius, flexible cable installation	≥ 75 mm
Prečnik kabela	6 mm
Struktura kabela	1x4x0,14+4x0,34 zaslonjeno
Nazivni presek provodnika	0,14 mm ² 0,34 mm ²
Mehanička zaštita	IP65
Note on degree of protection	IP30 for plug connector Sub-D u montiranom stanju
Temperatura okoline	-40 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-10 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Stepen zagađenja	3
Material cable sheath	TPE-U(PUR)