

Plastično crevo PEN-10X1,5-BL-300

Broj artikla: 551447

FESTO

Standardna O.D creva, za QSa utične priključke, polietilen
(nedopušteno kod proizvodnje prehrambenih artikala).



Tehnički podaci

| Svojstvo | Vrednost |
|--|--|
| Spoljašnji prečnik | 10 mm |
| Radius savijanja, merodavan za protok | 40 mm |
| Unutrašnji prečnik | 7 mm |
| Min. radius savijanja | 23,5 mm |
| Tubing characteristics | Suitable for energy chains |
| Temperature-dependent operating pressure | -0,095 ... 1 MPa |
| Pogonski pritisak zavisao od temperature | -0,95 ... 10 bar |
| Temperature-dependent operating pressure | -13,775 ... 145 psi |
| Napomena za pogonski pritisak | Water: max. 0.6 MPa at 0 - 50 °C |
| Dozvola | TÜV |
| Mesto izdavanja sertifikata | B 013277 0506 00 |
| Pogonski medijum | Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice) |
| PWIS conformity | VDMA24364-B2-L |
| Cleanroom class | This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Temperatura okoline | -30 ... 60 °C |
| Težina proizvoda prema dužini | 0,03766 kg/m |
| Pneumatski priključak | For push-in connector outside diameter 10 mm |
| Boja | plavo |
| Tvrdoća po Shoreu | D 52 +/-3 |
| Materijal - napomena | RoHS komfornost |
| Material tubing | PE |