

Plastično crevo PEN-16X2,5-SI-100

Broj artikla: 551455

FESTO

Standardna O.D creva, za QSa utične priključke, polietilen
(nedopušteno kod proizvodnje prehrambenih artikala).



Tehnički podaci

Svojstvo	Vrednost
Spoljašnji prečnik	16 mm
Radius savijanja, merodavan za protok	122 mm
Unutrašnji prečnik	10,8 mm
Min. radius savijanja	57,5 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0,095 ... 1 MPa
Pogonski pritisak zavisao od temperature	-0,95 ... 10 bar
Temperature-dependent operating pressure	-13,775 ... 145 psi
Napomena za pogonski pritisak	Water: max. 0.6 MPa at 0 - 50 °C
Dozvola	TÜV
Mesto izdavanja sertifikata	B 013277 0506 00
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7::-:] Water (liquid, free of ice)
PWIS conformity	VDMA24364-B2-L
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Temperatura okoline	-30 ... 60 °C
Težina proizvoda prema dužini	0,1029 kg/m
Pneumatski priključak	For push-in connector outside diameter 16 mm
Boja	srebrno
Tvrdoća po Shoreu	D 52 +/-3
Materijal - napomena	RoHS komformnost
Material tubing	PE