

Plastično crevo PEN-12X1,75-RT

Broj artikla: 551478

FESTO

Standardna O.D creva, za QSa utične priključke, polietilen
(nedopušteno kod proizvodnje prehrambenih artikala).



Tehnički podaci

Svojstvo	Vrednost
Spoljašnji prečnik	12 mm
Radius savijanja, merodavan za protok	58 mm
Unutrašnji prečnik	8,4 mm
Min. radius savijanja	33 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0,095 ... 1 MPa
Pogonski pritisak zavisao od temperature	-0,95 ... 10 bar
Temperature-dependent operating pressure	-13,775 ... 145 psi
Napomena za pogonski pritisak	Water: max. 0.6 MPa at 0 - 50 °C
Dozvola	TÜV
Mesto izdavanja sertifikata	B 013277 0506 00
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice)
PWIS conformity	VDMA24364-B2-L
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Temperatura okoline	-30 ... 60 °C
Težina proizvoda prema dužini	0,05423 kg/m
Pneumatski priključak	For push-in connector outside diameter 12 mm
Boja	crveno
Tvrdoća po Shoreu	D 52 +/-3
Materijal - napomena	RoHS komfornost
Material tubing	PE