

Vod enkodera



NEBM-M12G8-E-10-N-S1G15

Broj artikla: 8003763

Komponenta koja će prestati da se proizvodi

[Odgovara servo motoru EMMS-AS-...](#)

FESTO



Tehnički podaci

Svojstvo	Vrednost
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 2, function	Controller side
Electrical connection 2, design	ugaono
Electrical connection 2, connection type	Utikači
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	Sub-D
Electrical connection 2, number of pins/wires	15
Electrical connection 2, occupied pins/wires	8
Područje pogonskog napona DC	0 ... 30 V
Nazivni pogonski napon DC	24 V
Područje pogonskog napona AC	0 ... 30 V
Nazivni pogonski napon AC	24 V
Dužina kabela	10 m
Svojstvo kabela	Suitable for energy chains
Bending radius, flexible cable installation	≥ 68 mm
Prečnik kabela	6,8 mm
Struktura kabela	4x2x0,14 zaslonjeno
Nazivni presek provodnika	0,14 mm ²
Mehanička zaštita	IP65
Note on degree of protection	IP30 for plug connector Sub-D u montiranom stanju
Temperatura okoline	-40 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Klasa korozione otpornosti KBK	0 - No corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo