

# Spojni vod

## NEBV-Z4WA2L-P-E-10-N-LE2-S1

Broj artikla: 8047670

FESTO



### Tehnički podaci

| Svojstvo                                       | Vrednost  |
|--|---|
| Signal status display                          | LED žuti  |
| Dodatne funkcije                               | Zaštitni krug                                       |
| Cable identification                           | Without inscription label holder                    |
| Frekvencija priključivanja                     | 50  |
| Težina proizvoda                               | 170 g   |
| Electrical connection 1, function              | Field device side                                   |
| Electrical connection 1, design                | ugaono  |
| Electrical connection 1, connection type       | Utičnica  |
| Electrical connection 1, cable outlet          | Angled  |
| Electrical connection 1, connection technology | Connection pattern ZC, metric screw                 |
| Electrical connection 1, number of pins/wires  | 2   |
| Electrical connection 1, occupied pins/wires   | 2   |
| Electrical connection 1, type of mounting      | na elektromagnetnom ventilu sa središnjim vijkom M2 |
| Electrical connection 2, function              | Controller side                                     |
| Electrical connection 2, connection type       | Kabl  |
| Electrical connection 2, connection technology | otvoreni kraj                                       |
| Electrical connection 2, number of pins/wires  | 2   |
| Electrical connection 2, occupied pins/wires   | 2   |
| Područje pogonskog napona DC                   | 20,4 ... 26,4 V                                     |
| Nazivni pogonski napon DC                      | 24 V  |
| Čvrstoća na udarno naprezanje                  | 2,4 kV  |
| Zaštita od zamene polova                       | bipolarno   |
| Priključak uzemljenja                          | ne postoji  |
| Dužina kabla                                   | 10 m  |
| Svojstvo kabla                                 | Suitable for energy chains                          |
| Uslovi ispitivanja kabla                       | Uslovi ispitivanja na zahtev                        |
| Bending radius, flexible cable installation    | ≥ 29 mm   |
| Prečnik kabla                                  | 2,9 mm  |
| Odstupanje prečnika kabla                      | ± 0,1 mm  |
| Struktura kabla                                | 2x0,14  |
| Nazivni presek provodnika                      | 0,14 mm <sup>2</sup>                                |
| Mehanička zaštita                              | IP65  |
| Note on degree of protection                   | u montiranom stanju                                 |
| Temperatura okoline                            | -10 ... 50 °C                                       |
| CE znak (vidi izjavu o usklađenosti)           | in accordance with EU RoHS directive                |
| UKCA marking (see declaration of conformity)   | To UK RoHS instructions                             |
| PWIS conformity                                | VDMA24364-B2-L                                      |
| Materijal - napomena                           | RoHS komfornost                                     |
| Stepen zagađenja                               | 3   |
| Klasa korozione otpornosti KBK                 | 3 - High corrosion stress                           |
| Material cable sheath                          | TPE-U(PUR)  |
| Boja izolacije                                 | sivo  |
| Material housing                               | TPE-U(PU)   |
| Boja kućišta                                   | crno  |
| Material screws                                | Nerdajući čelik                                     |
| Material electrical contact                    | Legura bakra, kalajisana                            |
| Material insulation                            | PP  |