


# Spojni vod

## NEBV-Z4WA2L-P-E-0.5-N-M8G3-S1

Broj artikla: 8047673

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Signal status display	LED žuti
Dodatne funkcije	Zaštitni krug
Cable identification	Without inscription label holder
Frekvencija priključivanja	50
Težina proizvoda	18 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Connection pattern ZC, metric screw
Electrical connection 1, number of pins/wires	2
Electrical connection 1, occupied pins/wires	2
Electrical connection 1, type of mounting	na elektromagnetnom ventilu sa središnjim vijkom M2
Electrical connection 2, function	Controller side
Electrical connection 2, design	okruglo
Electrical connection 2, connection type	Utikači
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	M8x1, A-coded to EN 61076-2-104
Electrical connection 2, number of pins/wires	3
Electrical connection 2, occupied pins/wires	2
Područje pogonskog napona DC	20,4 ... 26,4 V
Nazivni pogonski napon DC	24 V
Čvrstoća na udarno naprezanje	2,4 kV
Zaštita od zamene polova	bipolarno
Priključak uzemljenja	ne postoji
Dužina kabla	0,5 m
Svojstvo kabla	Suitable for energy chains
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, flexible cable installation	≥ 29 mm
Prečnik kabla	2,9 mm
Odstupanje prečnika kabla	± 0,1 mm
Struktura kabla	2x0,14
Nazivni presek provodnika	0,14 mm <sup>2</sup>
Mehanička zaštita	IP65
Note on degree of protection	u montiranom stanju
Temperatura okoline	-10 ... 50 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	3 - High corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo
Material housing	TPE-U(PU)
Boja kućišta	crno

Svojstvo	Vrednost
Material of union nut	Mesing niklovan
Material screws	Nerđajući čelik
Material electrical contact	Legura bakra, kalajisana Brass, gold-plated
Material insulation	PP