

Plastično crevo

PTFEN-5/16-NT-150

Broj artikla: 8063351

FESTO



Tehnički podaci

Svojstvo	Vrednost
Spoljašnji prečnik	7,94 mm
Radius savijanja, merodavan za protok	90 mm
Unutrašnji prečnik	5,9 mm
Min. radius savijanja	64 mm
Uputstva za korišćenje	Tubing without printing
Operating pressure for entire temperature range	-0,095 ... 0,5 MPa
Pogonski pritisak kompletnog temperaturnog područja	-0,95 ... 5 bar
Operating pressure for entire temperature range	-13,775 ... 72,5 psi
Temperature-dependent operating pressure	-0,095 ... 1,2 MPa
Pogonski pritisak zavisn od temperature	-0,95 ... 12 bar
Temperature-dependent operating pressure	-13,775 ... 174 psi
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7::-]
Material fire test	UL94 V-0
PWIS conformity	VDMA24364-B1/B2-L
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See Supplementary material information
Temperatura okoline	-20 ... 150 °C
Težina proizvoda prema dužini	0,049 kg/m
Pneumatski priključak	For push-in connector outside diameter 5/16"
Boja	prirodno
Tvrdoća po Shoreu	D 55 +/-5
Materijal - napomena	RoHS komformnost
Material tubing	PTFE