

Svojstvo	Vrednost
Ethernet interface, function	Dijagnoza Programming
Ethernet interface, type of connection	Utičnica
Ethernet interface, connection technology	RJ45
Ethernet interface, number of pins/wires	8
Ethernet interface, transmission rate	10 Mbit/s 100 Mbit/s 1000 Mbit/s
Storage medium	microSD
Memory capacity	<= 32.000.000.000 Byte
Temperatura ležaja	-20 ... 70 °C
Mehanička zaštita	IP20
Temperatura okoline	-5 ... 50 °C
Relativna vlažnost vazduha	95 % ne kondenzira se
PWIS conformity	VDMA24364-B2-L
Material housing	PA ojačan
Materijal - napomena	RoHS komfornost