

Position indicator SAMH-F12-MK

Broj artikla: 8092711

FESTO



Tehnički podaci

Svojstvo	Vrednost
Položaj ugradnje	proizvoljno
Konstruktivna struktura	Without sensors
Uputstva za korišćenje	The SIL certification for the entire product is invalidated when used with angle seat valve VZXA.
Materijal - napomena	RoHS komformnost
Temperatura okoline	-20 ... 60 °C
Temperatura ležaja	-10 ... 60 °C
Težina proizvoda	118 g
Material seals	EPDM
Material housing	Aluminijum PA ojačan
Mehanička zaštita	IP65 IP67
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
PWIS conformity	VDMA24364 zone III