


Vertikalno napojna ploča VMPA14-VSP-QS8

Broj artikla: 8110622

FESTO



Tehnički podaci

Svojstvo	Vrednost
Mera mreže	14 mm
Operating pressure MPa	-0,09 ... 1 MPa
Pogonski pritisak	-0,9 ... 10 bar
Pilot pressure MPa	0,3 ... 0,8 MPa
Pritisak upravljanja	3 ... 8 bar
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7:4:4]
Klasa korozione otpornosti KBK	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Temperatura okoline	-5 ... 50 °C
Težina proizvoda	50 g
Pneumatski priključak 1	QS-8
Materijal - napomena	RoHS komfornost
Material supply plate	PA ojačan