

# Plastično crevo PUN-H-F-4X0,75-SW

Broj artikla: 8153385

FESTO

Ovaj proizvod se može koristiti sa priključcima serije: QS, NPQP, NPQM, CRQS i CK.



## Tehnički podaci

Svojstvo	Vrednost
Spoljašnji prečnik	4 mm
Radius savijanja, merodavan za protok	16 mm
Unutrašnji prečnik	2,6 mm
Min. radius savijanja	8 mm
Uputstva za korišćenje	Tubing without printing TPE-U Ether basiert
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0,095 ... 0,6 MPa
Pogonski pritisak kompletnog temperaturnog područja	-0,95 ... 6 bar
Operating pressure for entire temperature range	-13,775 ... 87 psi
Temperature-dependent operating pressure	-0,095 ... 1 MPa
Pogonski pritisak zavisao od temperature	-0,95 ... 10 bar
Temperature-dependent operating pressure	-13,775 ... 145 psi
Napomena za pogonski pritisak	Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60°C
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice)
Material fire test	UL94 HB
PWIS conformity	VDMA24364-B2-L
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See declaration of conformity
Temperatura okoline	-35 ... 60 °C
Težina proizvoda prema dužini	0,0084 kg/m
Pneumatski priključak	For push-in connector outside diameter 4 mm za spajanje navlačenjem, unutrašnji prečnik 3 mm sa maticom
Boja	crno
Tvrdoća po Shoreu	D 52 +/-3
Materijal - napomena	RoHS komformnost
Material tubing	TPE-U(PU)