

Plastično crevo PUN-H-SF-8X1,55-SW

Broj artikla: 8167901

FESTO



Tehnički podaci

Svojstvo	Vrednost
Spoljašnji prečnik	8 mm
Radius savijanja, merodavan za protok	35 mm
Unutrašnji prečnik	4,9 mm
Min. radius savijanja	15 mm
Uputstva za korišćenje	TPE-U Ether basiert
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0,095 ... 0,6 MPa
Pogonski pritisak kompletnog temperaturnog područja	-0,95 ... 6 bar
Operating pressure for entire temperature range	-13,775 ... 87 psi
Temperature-dependent operating pressure	-0,095 ... 1,3 MPa
Pogonski pritisak zavisn od temperature	-0,95 ... 13 bar
Temperature-dependent operating pressure	-13,775 ... 188,5 psi
Napomena za pogonski pritisak	Water: temperature-dependent operating pressure, see diagram, max. 0.7 MPa at 0 - 60°C
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice)
Material fire test	UL94 HB
PWIS conformity	VDMA24364-B2-L
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See Supplementary material information
Temperatura okoline	-35 ... 80 °C
Težina proizvoda prema dužini	0,04 kg/m
Pneumatski priključak	For push-in connector outside diameter 8 mm
Boja	crno
Tvrdoća po Shoreu	D 54 +/-3
Materijal - napomena	RoHS komfornost
Material tubing	TPE-U(PU)