

氣條

VABM-C8-12E-G14-6-PT-L

料號: 1247976

Classic - nicht für Neukonstruktionen verwenden

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



技術參數

| 特性 | 值 |
|--|---|
| 網柵尺寸 | 12 mm |
| 閥位的最大數量 | 6 |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC To UK RoHS instructions |
| 耐腐蝕等級 CRC | 0 - No corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| 最大緊固扭矩, 閥安裝 | 0.6 Nm |
| 最大緊固扭矩, 牆面安裝 | 5 Nm |
| 產品重量 | 627 g |
| 氣壓連接, 氣口 1 | G1/4 |
| 氣壓連接, 氣口 3 | G1/4 |
| 氣壓連接, 氣口 5 | G1/4 |
| 材料備註 | 符合 RoHS |
| Material manifold | 鍛造鋁合金 |