

# 氣條

## VABM-C8-12E-G14-16-PT-L

料號: 1247981

Classic - nicht für Neukonstruktionen verwenden

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



### 技術參數

| 特性   | 值   |
|--|---|
| 網柵尺寸   | 12 mm   |
| 閥位的最大數量                                      | 16  |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC<br>To UK RoHS instructions |
| 耐腐蝕等級 CRC                                    | 0 - No corrosion stress                               |
| PWIS conformity                              | VDMA24364-B1/B2-L                                     |
| 最大緊固扭矩, 閥安裝                                  | 0.6 Nm  |
| 最大緊固扭矩, 牆面安裝                                 | 5 Nm  |
| 產品重量   | 1,145 g   |
| 氣壓連接, 氣口 1                                   | G1/4  |
| 氣壓連接, 氣口 3                                   | G1/4  |
| 氣壓連接, 氣口 5                                   | G1/4  |
| 材料備註   | 符合 RoHS   |
| Material manifold                            | 鍛造鋁合金   |