

# 塑料氣管 PAN-V0-6X1-SW

料號: 160550

FESTO

阻燃劑



## 技術參數

特性	值
外徑	8 mm
插入式接頭的外徑	6 mm
與流量相關的彎曲半徑	30 mm
內徑	4 mm
最小彎曲半徑	13 mm
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0.095 ... 0.3 MPa
操作壓力的完整溫度範圍	-0.95 ... 3 bar
Operating pressure for entire temperature range	-13.775 ... 43.5 psi
Temperature-dependent operating pressure	-0.095 ... 1.2 MPa
溫度取決於操作壓力	-0.95 ... 12 bar
Temperature-dependent operating pressure	-13.775 ... 174 psi
操作壓力注意事項	Mineral oil: max. 0.3 MPa at max. 90°C Water: max. 0.3 MPa at max. 90°C
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] 礦物油 Water (liquid, free of ice)
Material fire test	UL94 V-0 (casing)
PWIS conformity	VDMA24364-B2-L
環境溫度	-30 ... 90 °C
產品重量視長度而定	0.049 kg/m
氣壓連接	For push-in connector outside diameter 6 mm
顏色	黑色
肖氏硬度	A 72 +/-4 D 57 +/-3
材料備註	符合 RoHS
Material tubing	多醯胺 12 PVC-P