

密封圈  
OL-1/8  
料號: 33840

FESTO

防洩漏, 具金屬殼體



技術參數

特性	值
基於標準	ISO 16030
Operating pressure for entire temperature range	-0.095 ... 3 MPa
操作壓力的完整溫度範圍	-0.95 ... 30 bar
Operating pressure for entire temperature range	-13.775 ... 435 psi
耐腐蝕等級 CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F1a
無塵室等級	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
環境溫度	-40 ... 100 °C
環境溫度下手動緊固	是
額定鎖緊扭矩	6 Nm
額定擰緊扭矩公差	± 20 %
產品重量	0.14 g
氣壓連接	G1/8
材料備註	符合 RoHS
Material stops	鋁
Material seals	HNBR