



馬達電纜

NEBM-S1G9-E-25-Q5-LE6

料號: 5085057

FESTO



技術參數

特性	值
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	有角的
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	直的
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	9
Electrical connection 1, occupied pins/wires	6
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	電纜
Electrical connection 2, connection technology	開放式終端
Electrical connection 2, number of pins/wires	6
Electrical connection 2, occupied pins/wires	6
工作電壓範圍 DC	0 ... 72 V
額定工作電壓 DC	24 V
電纜長度	25 m
電纜屬性	Suitable for energy chains
Bending radius, flexible cable installation	>= 62 mm
電纜直徑	6.2 mm
電纜結構	6x0,34 已屏蔽
導體的額定截面	0.34 mm ²
導線末端	導線末端套圈
防護等級	IP65
Note on degree of protection	裝配狀態
環境溫度	-40 ... 80 °C
Ambient temperature with flexible cable installation	-5 ... 80 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS
耐腐蝕等級 CRC	0 - No corrosion stress
Material cable sheath	TPE-U(PUR)
電纜外套顏色	灰色